

Case Study

Tone Wheel




Material: Ferrophosphorus material
for magnetic properties

Process: Warm Compaction

UTS: 380 MPa

Previous Process:

Mold to 6.8g/cc
Sinter
Machine
Resin impregnate
Oil Leak Test



New Process:

Mold to 7.1g/cc minimum with Warm
Compaction
Sinter
Machine

Benefit:

Warm Compaction with increased density eliminates the possibility of interconnected porosity and therefore, it also eliminates the need for resin impregnation or leak check.



Case Study

Carrier Assembly



Material: Iron Copper Mix

Process: Warm Compaction
with Sinterbrazing

UTS: 600 MPa

Previous Process:

Mold Grey Iron Casting
Machine top and bottom
surfaces, inside top
and bottom, outer
spline, and mill holes.



New Process:

Mold Spider with Warm Compaction
Mold Flange
Sinterbraze with copper infiltration
Machine top face, bearing surface, and
mill holes

Benefit:

Warm Compaction provides high strength and the brazing of two components molded from powdered metal eliminates the need for much of the machining for a cost savings.



Case Study

Sleeve




Material: High Alloy Mix

Process: Warm Compaction,
Elevated Temperature Sinter

UTS: 1560 MPa

Previous Process:

Mold Forging
Machine OD, Length, Groove.
Machine ID Spline
Machine Top Spline



New Process:

Mold Part with Warm Compaction for
High Density on Top Spline.
Sinter with Elevated Temperature
Machine Groove

Benefit:

Molding by Warm Compaction to an extremely high density of 7.4 minimum provides high strength and meets the very high tensile strength requirements at the top of the teeth in the top spline. Elevated temperature sintering produces a pore rounding in the microstructure that provides added strength to the part and the teeth. The only machining required is the OD groove, resulting in an overall cost savings.